



## **Stainless steel Bearing**

**POPULAR SIZE**



**NINGBO ACCOR BEARING CO.,LTD**

**CAT.NO.2011SEP**

|                                                            |          |
|------------------------------------------------------------|----------|
| <b>Stainless steel Bearing .....</b>                       | <b>2</b> |
| 不锈钢轴承                                                      |          |
| Deep groove stainless steel ball bearings.....             | 3-5      |
| 不锈钢深沟球轴承尺寸表                                                |          |
| Angular contact stainless steel ball bearings .....        | 6-7      |
| 不锈钢角触球轴承尺寸表                                                |          |
| Self-aligning stainless steel ball bearings.....           | 8-9      |
| 不锈钢调心球轴承尺寸表                                                |          |
| Single direction thrust stainless steel ball bearings..... | 10       |
| 不锈钢推力球轴承尺寸表                                                |          |
| Insert stainless steel bearing.....                        | 11       |
| 不锈钢外球面轴承尺寸表                                                |          |

### Stainless steel bearings(440C)

The high performance stainless steel bearings can provides not only with the cleanliness and corrosion resistance characteristic also with the high accuracy and excellent wear resistance compare to the high carbon chrome steel bearings. The rings and balls are made of the material as a standard structure of stainless steel bearing, The rings and balls are made of the material of AISI440C( 9Cr18Mo or 9Cr18), the cage and the framework of seal adoption the AI304 or AI316, production accuracy could reach ISO standard ABEC-1 and above, and the vibration level reach Z1 grade and above.

### Austenite stainless steel bearings

We also can offer non-standard stainless steel bearings to meet some special type needs in engineering. Compare to high carbon chrome martensite stainless steel bearing, Austenite stainless steel bearings have even more excellent corrosion and wear resistance, magnetism resistance. The whole Austenite stainless steel bearings are made of AISI SUS316L(316)or SUS304 ( including inside and outside rings , balls and cage). Austenite stainless steel bearings can't harden completely by heat treatment, so it should not choose for heavier load or higher speed.

### Stainless plummer block and stainless insert bearings

Stainless Bearing Units have some advantages, Such as automatic adjustment, Repeated lubrication, Dustproof and convenience for fixing and disassembly. It is widely used in various mechanical equipments and conveying device. Stainless Plummer blocks are specially designed to meet particular engineering demand for food. Medical and chemical industry. Which have some excellence such as cleanness, Anti-corrosion etc. Bearing housing is made of AISI304 and the insert bearings are made of AISI SUS440C, Specially AISI SUS316 also could be used.

### 不锈钢轴承

高性能的不锈钢轴承在清洁耐蚀的基础上同样提供可与高碳铬钢媲美的高精度及耐磨性， 作为标准结构的不锈钢轴承，套圈及滚动体材料采用AISI SUS440C（9Cr18Mo或9Cr18）经真空淬回火处理，保持架及密封圈骨架材料采用AISI304或AISI316，精度达ISO标准ABEC-1以上。振动等级Z1组及以上。


### 奥氏体不锈钢轴承

我们同样提供非标准形式不锈钢轴承以满足工程上的特种需求，相比较高碳铬马氏体不锈钢（如440C，420等），奥氏体不锈钢具有更优良的耐腐蚀性能及抗磁性。奥氏体不锈钢轴承整体采用AISI SUS316L（316）或SUS304材料制作（包括内外圈，球，及保持架）。因奥氏体不锈钢无法整体淬硬，故该轴承不适用于较大负荷及较高转速。

### 不锈钢轴承座及不锈钢外球面轴承

带座外球面轴承具有自动调心，多次重复润滑，防尘密封良好，安装拆卸方便等优点。被广泛用于各种机械设备及传送装置。不锈钢带座轴承是专门开发用以满足食品、医疗、化工等行业的特殊需求。在保证普通铬钢带座轴承耐磨性能的同时，同样具备耐腐蚀、清洁的优点。轴承座采用AISI304材料，外球面轴承使用AISI440C材料。特殊用途也可使用AISI316材料。

Deep groove stainless steel ball bearings




| Bearing No | Boundary dimensions(mm) |    |     |         | Mounting dimensions(mm) |      |      |      | mass    |
|------------|-------------------------|----|-----|---------|-------------------------|------|------|------|---------|
|            |                         |    |     |         | da                      | da   | Da   | ra   | (kg)    |
|            | d                       | D  | B   | r (min) | min                     | max  | max  | max  | (refer) |
| SS684      | 4                       | 9  | 2.5 | 0.1     | 4.8                     | /    | 8.2  | 0.1  | 0.0001  |
| SS694      |                         | 11 | 4   | 0.15    | 5.2                     | /    | 9.8  | 0.15 | 0.0003  |
| SS604      |                         | 12 | 4   | 0.2     | 5.6                     | /    | 10.4 | 0.2  | 0.0004  |
| SS624      |                         | 13 | 5   | 0.2     | 5.6                     | /    | 11.4 | 0.2  | 0.0006  |
| SS634      |                         | 16 | 5   | 0.3     | 6                       | /    | 14   | 0.3  | 0.001   |
| SS685      | 5                       | 11 | 3   | 0.15    | 6.2                     | /    | 9.8  | 0.15 | 0.0002  |
| SS695      |                         | 13 | 4   | 0.2     | 6.6                     | /    | 11.4 | 0.2  | 0.0005  |
| SS605      |                         | 14 | 5   | 0.2     | 6.6                     | /    | 12.4 | 0.2  | 0.0007  |
| SS625      |                         | 16 | 5   | 0.3     | 7                       | /    | 14   | 0.3  | 0.001   |
| SS635      |                         | 19 | 6   | 0.3     | 7                       | /    | 17   | 0.3  | 0.0016  |
| SS686      | 6                       | 13 | 3.5 | 0.15    | 7.2                     | /    | 11.8 | 0.15 | 0.0004  |
| SS696      |                         | 15 | 5   | 0.2     | 7.6                     | /    | 13.4 | 0.2  | 0.0007  |
| SS606      |                         | 17 | 6   | 0.3     | 8                       | /    | 15   | 0.3  | 0.0011  |
| SS626      |                         | 19 | 6   | 0.3     | 8                       | /    | 17   | 0.3  | 0.0016  |
| SS636      |                         | 22 | 7   | 0.3     | 8                       | /    | 20   | 0.3  | 0.0027  |
| SS687      | 7                       | 14 | 3.5 | 0.15    | 8.2                     | /    | 12.8 | 0.15 | 0.0004  |
| SS697      |                         | 17 | 5   | 0.3     | 9                       | /    | 15   | 0.3  | 0.001   |
| SS607      |                         | 19 | 6   | 0.3     | 9                       | /    | 17   | 0.3  | 0.0015  |
| SS627      |                         | 22 | 7   | 0.3     | 9                       | /    | 20   | 0.3  | 0.0024  |
| SS637      |                         | 26 | 9   | 0.3     | 9                       | /    | 24   | 0.3  | 0.0046  |
| SS688      | 8                       | 16 | 4   | 0.2     | 9.6                     | /    | 14.4 | 0.2  | 0.0006  |
| SS698      |                         | 19 | 6   | 0.3     | 10                      | /    | 17   | 0.3  | 0.0014  |
| SS608      |                         | 22 | 7   | 0.3     | 10                      | /    | 20   | 0.3  | 0.0023  |
| SS628      |                         | 24 | 8   | 0.3     | 10                      | /    | 22   | 0.3  | 0.0033  |
| SS638      |                         | 28 | 9   | 0.3     | 10                      | /    | 26   | 0.3  | 0.0054  |
| SS689      | 9                       | 17 | 4   | 0.2     | 10.6                    | /    | 15.4 | 0.2  | 0.0007  |
| SS699      |                         | 20 | 6   | 0.3     | 11                      | /    | 18   | 0.3  | 0.0016  |
| SS609      |                         | 24 | 7   | 0.3     | 11                      | /    | 22   | 0.3  | 0.0028  |
| SS629      |                         | 26 | 8   | 0.3     | 11                      | /    | 24   | 0.3  | 0.0038  |
| SS639      |                         | 30 | 10  | 0.6     | 13                      | /    | 26   | 0.6  | 0.007   |
| SS6800     | 10                      | 19 | 5   | 0.3     | 12                      | 12   | 17   | 0.3  | 0.001   |
| SS6900     |                         | 22 | 6   | 0.3     | 12                      | 12.5 | 20   | 0.3  | 0.0017  |
| SS6000     |                         | 26 | 8   | 0.3     | 12                      | 13   | 24   | 0.3  | 0.0035  |
| SS6200     |                         | 30 | 9   | 0.6     | 14                      | 16   | 26   | 0.6  | 0.006   |
| SS6300     |                         | 35 | 11  | 0.6     | 14                      | 16.5 | 31   | 0.6  | 0.01    |
| SS6801     | 12                      | 21 | 5   | 0.3     | 14                      | 14   | 19   | 0.3  | 0.0012  |
| SS6901     |                         | 24 | 6   | 0.3     | 14                      | 14.5 | 22   | 0.3  | 0.0019  |
| SS16001    |                         | 28 | 7   | 0.3     | 14                      | /    | 26   | 0.3  | 0.004   |
| SS6001     |                         | 28 | 8   | 0.3     | 14                      | 15.5 | 26   | 0.3  | 0.004   |
| SS6201     |                         | 32 | 10  | 0.6     | 16                      | 17   | 28   | 0.6  | 0.007   |
| SS6301     |                         | 37 | 12  | 1       | 17                      | 18   | 32   | 1    | 0.012   |

| Bearing No | Boundary dimensions(mm) |     |    |         | Mounting dimensions(mm) |      |      |     | mass    |
|------------|-------------------------|-----|----|---------|-------------------------|------|------|-----|---------|
|            |                         |     |    |         | da                      | da   | Da   | ra  | (kg)    |
|            | d                       | D   | B  | r (min) | min                     | max  | max  | max | (refer) |
| SS6802     | 15                      | 24  | 5  | 0.3     | 17                      | 17   | 22   | 0.3 | 0.0013  |
| SS6902     |                         | 28  | 7  | 0.3     | 17                      | 17   | 26   | 0.3 | 0.003   |
| SS16002    |                         | 32  | 8  | 0.3     | 17                      | /    | 30   | 0.3 | 0.005   |
| SS6002     |                         | 32  | 9  | 0.3     | 17                      | 19   | 30   | 0.3 | 0.006   |
| SS6202     |                         | 35  | 11 | 0.6     | 19                      | 20.5 | 31   | 0.3 | 0.009   |
| SS6302     |                         | 42  | 13 | 1       | 20                      | 22.5 | 37   | 1   | 0.016   |
| SS6803     | 17                      | 26  | 5  | 0.3     | 19                      | 19   | 24   | 0.3 | 0.0013  |
| SS6903     |                         | 30  | 7  | 0.3     | 19                      | 19.5 | 28   | 0.3 | 0.0033  |
| SS16003    |                         | 35  | 8  | 0.3     | 19                      | /    | 33   | 0.3 | 0.006   |
| SS6003     |                         | 35  | 10 | 0.3     | 19                      | 21.5 | 33   | 0.3 | 0.008   |
| SS6203     |                         | 40  | 12 | 0.6     | 21                      | 23.5 | 36   | 0.6 | 0.013   |
| SS6303     |                         | 47  | 14 | 1       | 22                      | 25.5 | 42   | 1   | 0.022   |
| SS6403     | 20                      | 62  | 17 | 1.1     | 23.5                    | /    | 55.5 | 1   | 0.052   |
| SS6804     |                         | 32  | 7  | 0.3     | 22                      | 22.5 | 30   | 0.3 | 0.003   |
| SS6904     |                         | 37  | 9  | 0.3     | 22                      | 24   | 35   | 0.3 | 0.007   |
| SS16004    |                         | 42  | 8  | 0.3     | 22                      | /    | 40   | 0.3 | 0.009   |
| SS6004     |                         | 42  | 12 | 0.6     | 24                      | 25.5 | 38   | 0.6 | 0.013   |
| SS6204     |                         | 47  | 14 | 1       | 25                      | 26.5 | 42   | 1   | 0.021   |
| SS6304     | 25                      | 52  | 15 | 1.1     | 26.5                    | 28   | 45.5 | 1   | 0.028   |
| SS6404     |                         | 72  | 19 | 1.1     | 26.5                    | /    | 65.5 | 1   | 0.08    |
| SS6805     |                         | 37  | 7  | 0.3     | 27                      | 27   | 35   | 0.3 | 0       |
| SS6905     |                         | 42  | 9  | 0.3     | 27                      | 28.5 | 40   | 0.3 | 0.01    |
| SS16005    |                         | 47  | 8  | 0.3     | 27                      | /    | 45   | 0.3 | 0.011   |
| SS6005     |                         | 47  | 12 | 0.6     | 29                      | 30   | 43   | 0.6 | 0.015   |
| SS6205     | 30                      | 52  | 15 | 1       | 30                      | 32   | 47   | 1   | 0.025   |
| SS6305     |                         | 62  | 17 | 1.1     | 31.5                    | 36   | 55.5 | 1   | 0.045   |
| SS6405     |                         | 80  | 21 | 1.5     | 33                      | /    | 72   | 1.5 | 0.102   |
| SS6806     |                         | 42  | 7  | 0.3     | 32                      | 32   | 50   | 1   | 0.005   |
| SS6906     |                         | 47  | 9  | 0.3     | 32                      | 34   | 57   | 1   | 0.01    |
| SS16006    |                         | 55  | 9  | 0.3     | 32                      | 42.5 | 65.5 | 1   | 0.017   |
| SS6006     | 35                      | 55  | 13 | 1       | 35                      | 36.5 | 53   | 1   | 0.022   |
| SS6206     |                         | 62  | 16 | 1       | 35                      | 38.5 | 60   | 1   | 0.038   |
| SS6306     |                         | 72  | 19 | 1.1     | 36.5                    | 42.5 | 68.5 | 1   | 0.066   |
| SS6406     |                         | 90  | 23 | 1.5     | 54                      | /    | 82   | 2   | 0.14    |
| SS6807     |                         | 47  | 7  | 0.3     | 37                      | 37   | 45   | 0.3 | 0.005   |
| SS6907     |                         | 55  | 10 | 0.6     | 39                      | 39   | 51   | 0.6 | 0.014   |
| SS16007    | 40                      | 62  | 9  | 0.3     | 37                      | /    | 60   | 0.3 | 0.021   |
| SS6007     |                         | 62  | 14 | 1       | 40                      | 41.5 | 57   | 1   | 0.029   |
| SS6207     |                         | 72  | 17 | 1.1     | 41.5                    | 44.5 | 65.5 | 1   | 0.055   |
| SS6307     |                         | 80  | 21 | 1.5     | 43                      | 47   | 72   | 1.5 | 0.089   |
| SS6407     |                         | 100 | 25 | 1.5     | 43                      | /    | 92   | 1.5 | 0.18    |
| SS6808     |                         | 52  | 7  | 0.3     | 42                      | 42   | 50   | 0.3 | 0.006   |
| SS6908     | 45                      | 62  | 12 | 0.6     | 44                      | 46   | 58   | 0.6 | 0.022   |
| SS16008    |                         | 68  | 9  | 0.3     | 42                      | /    | 66   | 0.3 | 0.025   |
| SS6008     |                         | 68  | 15 | 1       | 45                      | 47.5 | 63   | 1   | 0.037   |
| SS6208     |                         | 80  | 18 | 1.1     | 46.5                    | 50.5 | 73.5 | 1   | 0.07    |
| SS6308     |                         | 90  | 23 | 1.5     | 48                      | 53   | 80   | 1.5 | 0.12    |
| SS6408     |                         | 110 | 27 | 2       | 49                      | /    | 101  | 2   | 0.24    |
| SS6809     | 50                      | 58  | 7  | 0.3     | 47                      | 47.5 | 56   | 0.3 | 0.007   |
| SS6909     |                         | 68  | 12 | 0.6     | 49                      | 50   | 64   | 0.6 | 0.024   |
| SS16009    |                         | 75  | 10 | 0.6     | 49                      | /    | 71   | 0.6 | 0.032   |
| SS6009     |                         | 75  | 16 | 1       | 50                      | 53.5 | 70   | 1   | 0.046   |
| SS6209     |                         | 85  | 19 | 1.1     | 51.5                    | 55.5 | 78.5 | 1   | 0.081   |
| SS6309     |                         | 100 | 25 | 1.5     | 53                      | 61.5 | 92   | 1.5 | 0.16    |
| SS6409     | 55                      | 120 | 29 | 2       | 54                      | /    | 111  | 2   | 0.29    |

| Bearing No | Boundary dimensions(mm) |     |    |         | Mounting dimensions(mm) |      |       |     | mass    |
|------------|-------------------------|-----|----|---------|-------------------------|------|-------|-----|---------|
|            |                         |     |    |         | da                      | da   | Da    | ra  | (kg)    |
|            | d                       | D   | B  | r (min) | min                     | max  | max   | max | (refer) |
| SS6810     | 50                      | 65  | 7  | 0.3     | 52                      | 52.5 | 63    | 0.3 | 0.01    |
| SS6910     |                         | 72  | 12 | 0.6     | 54                      | 55   | 68    | 0.6 | 0.026   |
| SS16010    |                         | 80  | 10 | 0.6     | 54                      | /    | 76    | 0.6 | 0.034   |
| SS6010     |                         | 80  | 16 | 1       | 55                      | 58.5 | 75    | 1   | 0.05    |
| SS6210     |                         | 90  | 20 | 1.1     | 56.5                    | 60   | 83.2  | 1   | 0.088   |
| SS6310     |                         | 110 | 27 | 2       | 59                      | 68   | 101   | 2   | 0.2     |
| SS6410     |                         | 130 | 31 | 2.1     | 61                      | /    | 119   | 2   | 0.36    |
| SS6811     |                         | 72  | 9  | 0.3     | 57                      | 59   | 70    | 0.3 | 0.016   |
| SS6911     | 55                      | 80  | 13 | 1       | 60                      | 61.5 | 75    | 1   | 0.036   |
| SS16011    |                         | 90  | 11 | 0.6     | 59                      | /    | 86    | 0.6 | 0.049   |
| SS6011     |                         | 90  | 18 | 1.1     | 61.5                    | 64   | 83.5  | 1   | 0.073   |
| SS6211     |                         | 100 | 21 | 1.5     | 63                      | 66.5 | 92    | 1.5 | 0.12    |
| SS6311     |                         | 120 | 29 | 2       | 64                      | 72.5 | 111   | 2   | 0.26    |
| SS6411     |                         | 140 | 33 | 2.1     | 66                      | /    | 129   | 2   | 0.44    |
| SS6812     |                         | 78  | 10 | 0.3     | 62                      | 64   | 76    | 0.3 | 0.02    |
| SS6912     |                         | 85  | 13 | 1       | 65                      | 66   | 80    | 1   | 0.037   |
| SS16012    | 60                      | 95  | 11 | 0.6     | 64                      | /    | 91    | 0.6 | 0.054   |
| SS6012     |                         | 95  | 18 | 1.1     | 66.5                    | 69   | 88.5  | 1   | 0.079   |
| SS6212     |                         | 110 | 22 | 1.5     | 68                      | 74.5 | 102   | 1.5 | 0.15    |
| SS6312     |                         | 130 | 31 | 2.1     | 71                      | 79   | 119   | 2   | 0.33    |
| SS6412     |                         | 150 | 35 | 2.1     | 71                      |      | 139   | 2   | 0.53    |
| SS6813     |                         | 85  | 10 | 0.6     | 69                      | 69   | 81    | 0.6 | 0.025   |
| SS6913     |                         | 90  | 13 | 1       | 70                      | 71.5 | 85    | 1   | 0.04    |
| SS16013    |                         | 100 | 11 | 0.6     | 69                      | /    | 96    | 0.6 | 0.06    |
| SS6013     | 65                      | 100 | 18 | 1.1     | 71.5                    | 73   | 93.5  | 1   | 0.08    |
| SS6213     |                         | 120 | 23 | 1.5     | 73                      | 80   | 112   | 1.5 | 0.19    |
| SS6313     |                         | 140 | 33 | 2.1     | 76                      | 85.5 | 129   | 2   | 0.41    |
| SS6814     |                         | 90  | 10 | 0.6     | 74                      | 74.5 | 86    | 0.6 | 0.03    |
| SS6914     |                         | 100 | 16 | 1       | 75                      | 77.5 | 95    | 1   | 0.07    |
| SS16014    |                         | 110 | 13 | 0.6     | 74                      | /    | 106   | 0.6 | 0.08    |
| SS6014     |                         | 110 | 20 | 1.1     | 76.5                    | 80.5 | 103.5 | 1   | 0.12    |
| SS6214     |                         | 125 | 24 | 1.5     | 78                      | 84   | 117   | 1.5 | 0.21    |
| SS6314     | 70                      | 150 | 35 | 2.1     | 81                      | 92   | 139   | 2   | 0.49    |
| SS6815     |                         | 95  | 10 | 0.6     | 79                      | 79.5 | 91    | 0.6 | 0.029   |
| SS6915     |                         | 105 | 16 | 1       | 80                      | 82   | 100   | 1   | 0.07    |
| SS16015    |                         | 115 | 13 | 0.6     | 79                      | /    | 111   | 0.6 | 0.089   |
| SS6015     |                         | 115 | 20 | 1.1     | 81.5                    | 85.5 | 108.5 | 1   | 0.12    |
| SS6215     |                         | 130 | 25 | 1.5     | 83                      | 90   | 122   | 1.5 | 0.23    |
| SS6816     |                         | 100 | 10 | 0.6     | 84                      | 84.5 | 96    | 0.6 | 0.03    |
| SS6916     |                         | 110 | 16 | 1       | 85                      | 87.5 | 105   | 1   | 0.075   |
| SS16016    | 80                      | 125 | 14 | 0.6     | 84                      | /    | 121   | 0.6 | 0.12    |
| SS6016     |                         | 125 | 22 | 1.1     | 86.5                    | 91   | 118.5 | 1   | 0.17    |
| SS6216     |                         | 140 | 26 | 2       | 89                      | 95.5 | 131   | 2   | 0.27    |
| SS6817     |                         | 110 | 13 | 1       | 90                      | 90.5 | 105   | 1   | 0.051   |
| SS6917     |                         | 120 | 18 | 1.1     | 91.5                    | 94.5 | 113.5 | 1   | 0.11    |
| SS16017    |                         | 130 | 14 | 0.6     | 89                      | /    | 126   | 0.6 | 0.13    |
| SS6017     |                         | 130 | 22 | 1.1     | 91.5                    | 96   | 123.5 | 1   | 0.18    |
| SS6217     |                         | 150 | 28 | 2       | 94                      | 102  | 141   | 2   | 0.34    |
| SS6818     | 90                      | 115 | 13 | 1       | 95                      | 95.5 | 110   | 1   | 0.05    |
| SS6918     |                         | 125 | 18 | 1.1     | 96.5                    | 98.5 | 118.5 | 1   | 0.11    |
| SS16018    |                         | 140 | 16 | 1       | 95                      | /    | 135   | 1   | 0.17    |
| SS6018     |                         | 140 | 24 | 1.5     | 98                      | 103  | 132   | 1.5 | 0.23    |

## Angular contact stainless steel ball bearings




| Bearing No. | Boundary dimensions(mm) |    |    |       |          | Mounting dimensions(mm) |      |     | Mass<br>(kg)(refer) |
|-------------|-------------------------|----|----|-------|----------|-------------------------|------|-----|---------------------|
|             |                         |    |    | R     | R1       | da                      | Da   | ra  |                     |
|             | d                       | D  | B  | (min) | r1 (min) | min                     | max  | max |                     |
| SS7900      | 10                      | 22 | 6  | 0.3   | 0.15     | 12.5                    | 19.5 | 0.3 | 0.001               |
| SS7000      |                         | 26 | 8  | 0.3   | 0.15     | 12.5                    | 23.5 | 0.3 | 0.003               |
| SS7200      |                         | 30 | 9  | 0.6   | 0.3      | 15                      | 25   | 0.6 | 0.004               |
| SS7300      |                         | 35 | 11 | 0.6   | 0.3      | 15                      | 30   | 0.6 | 0.007               |
| SS7901      | 12                      | 24 | 6  | 0.3   | 0.15     | 14.5                    | 21.5 | 0.3 | 0.001               |
| SS7001      |                         | 28 | 8  | 0.3   | 0.15     | 14.5                    | 25.5 | 0.3 | 0.003               |
| SS7201      |                         | 32 | 10 | 0.6   | 0.3      | 17                      | 27   | 0.6 | 0.005               |
| SS7301      |                         | 37 | 12 | 1     | 0.6      | 18                      | 31   | 1   | 0.008               |
| SS7902      | 15                      | 28 | 7  | 0.3   | 0.15     | 17.5                    | 25.5 | 0.3 | 0.002               |
| SS7002      |                         | 32 | 9  | 0.3   | 0.15     | 17.5                    | 29.5 | 0.3 | 0.004               |
| SS7202      |                         | 35 | 11 | 0.6   | 0.3      | 20                      | 30   | 0.3 | 0.006               |
| SS7302      |                         | 42 | 13 | 1     | 0.6      | 21                      | 36   | 1   | 0.011               |
| SS7903      | 17                      | 30 | 7  | 0.3   | 0.15     | 19.5                    | 27.5 | 0.3 | 0.002               |
| SS7003      |                         | 35 | 10 | 0.3   | 0.15     | 19.5                    | 32.5 | 0.3 | 0.006               |
| SS7203      |                         | 40 | 12 | 0.6   | 0.3      | 22                      | 35   | 0.6 | 0.009               |
| SS7303      |                         | 47 | 14 | 1     | 0.6      | 23                      | 41   | 1   | 0.016               |
| SS7904      | 20                      | 37 | 9  | 0.3   | 0.15     | 22.5                    | 34.5 | 0.3 | 0.005               |
| SS7004      |                         | 42 | 12 | 0.6   | 0.3      | 25                      | 37   | 0.6 | 0.009               |
| SS7204      |                         | 47 | 14 | 1     | 0.6      | 26                      | 41   | 1   | 0.015               |
| SS7304      |                         | 52 | 15 | 1.1   | 0.6      | 27                      | 45   | 1   | 0.02                |
| SS7905      | 25                      | 42 | 9  | 0.3   | 0.15     | 27.5                    | 39.5 | 0.3 | 0.006               |
| SS7005      |                         | 47 | 12 | 0.6   | 0.3      | 30                      | 42   | 0.6 | 0.011               |
| SS7205      |                         | 52 | 15 | 1     | 0.6      | 31                      | 46   | 1   | 0.018               |
| SS7305      |                         | 62 | 17 | 1.1   | 0.6      | 32                      | 55   | 1   | 0.032               |
| SS7906      | 30                      | 47 | 9  | 0.3   | 0.15     | 32.5                    | 44.5 | 1   | 0.007               |
| SS7006      |                         | 55 | 13 | 1     | 0.6      | 36                      | 49   | 1   | 0.016               |
| SS7206      |                         | 62 | 16 | 1     | 0.6      | 36                      | 56   | 1   | 0.027               |
| SS7306      |                         | 72 | 19 | 1.1   | 0.6      | 37                      | 65   | 1   | 0.048               |
| SS7907      | 35                      | 55 | 10 | 0.6   | 0.3      | 40                      | 50   | 0.6 | 0.01                |
| SS7007      |                         | 62 | 14 | 1     | 0.6      | 41                      | 56   | 1   | 0.022               |
| SS7207      |                         | 72 | 17 | 1.1   | 0.6      | 42                      | 65   | 1   | 0.039               |
| SS7307      |                         | 80 | 21 | 1.5   | 1        | 44                      | 71   | 1.5 | 0.065               |
| SS7908      | 40                      | 62 | 12 | 0.6   | 0.3      | 45                      | 57   | 0.6 | 0.016               |
| SS7008      |                         | 68 | 15 | 1     | 0.6      | 46                      | 62   | 1   | 0.027               |
| SS7208      |                         | 80 | 18 | 1.1   | 0.6      | 47                      | 73   | 1   | 0.05                |
| SS7308      |                         | 90 | 23 | 1.5   | 1        | 49                      | 81   | 1.5 | 0.088               |

| Bearing No. | Boundary dimensions(mm) |     |    |       |          | Mounting dimensions(mm) |     |     | Mass<br>(kg)(refer) |
|-------------|-------------------------|-----|----|-------|----------|-------------------------|-----|-----|---------------------|
|             |                         |     |    | R     | R1       | da                      | Da  | ra  |                     |
|             | d                       | D   | B  | (min) | r1 (min) | min                     | max | max |                     |
| SS7909      | 45                      | 68  | 12 | 0.6   | 0.3      | 50                      | 63  | 0.6 | 0.017               |
| SS7009      |                         | 75  | 16 | 1     | 0.6      | 51                      | 69  | 1   | 0.034               |
| SS7209      |                         | 85  | 19 | 1.1   | 0.6      | 52                      | 78  | 1   | 0.057               |
| SS7309      |                         | 100 | 25 | 1.5   | 1        | 54                      | 91  | 1.5 | 0.115               |
| SS7910      | 50                      | 72  | 12 | 0.6   | 0.3      | 55                      | 67  | 0.6 | 0.018               |
| SS7010      |                         | 80  | 16 | 1     | 0.6      | 56                      | 74  | 1   | 0.036               |
| SS7210      |                         | 90  | 20 | 1.1   | 0.6      | 57                      | 83  | 1   | 0.063               |
| SS7310      |                         | 110 | 27 | 2     | 1        | 60                      | 100 | 2   | 0.147               |
| SS7911      | 55                      | 80  | 13 | 1     | 0.6      | 61                      | 74  | 1   | 0.027               |
| SS7011      |                         | 90  | 18 | 1.1   | 0.6      | 62                      | 83  | 1   | 0.052               |
| SS7211      |                         | 100 | 21 | 1.5   | 1        | 64                      | 91  | 1.5 | 0.086               |
| SS7311      |                         | 120 | 29 | 2     | 1        | 65                      | 110 | 2   | 0.188               |
| SS7912      | 60                      | 85  | 13 | 1     | 0.6      | 66                      | 79  | 1   | 0.027               |
| SS7012      |                         | 95  | 18 | 1.1   | 0.6      | 67                      | 88  | 1   | 0.057               |
| SS7212      |                         | 110 | 22 | 1.5   | 1        | 69                      | 101 | 1.5 | 0.108               |
| SS7312      |                         | 130 | 31 | 2.1   | 1.1      | 72                      | 118 | 2   | 0.237               |
| SS7913      | 65                      | 90  | 13 | 1     | 0.6      | 71                      | 84  | 1   | 0.031               |
| SS7013      |                         | 100 | 18 | 1.1   | 0.6      | 72                      | 93  | 1   | 0.061               |
| SS7213      |                         | 120 | 23 | 1.5   | 1        | 74                      | 111 | 1.5 | 0.138               |
| SS7313      |                         | 140 | 33 | 2.1   | 1.1      | 77                      | 128 | 2   | 0.291               |
| SS7914      | 70                      | 100 | 16 | 1     | 0.6      | 76                      | 94  | 1   | 0.048               |
| SS7014      |                         | 110 | 20 | 1.1   | 0.6      | 77                      | 103 | 1   | 0.084               |
| SS7214      |                         | 125 | 24 | 1.5   | 1        | 79                      | 116 | 1.5 | 0.151               |
| SS7314      |                         | 150 | 35 | 2.1   | 1.1      | 82                      | 138 | 2   | 0.355               |
| SS7915      | 75                      | 105 | 16 | 1     | 0.6      | 81                      | 99  | 1   | 0.05                |
| SS7015      |                         | 115 | 20 | 1.1   | 0.6      | 82                      | 108 | 1   | 0.09                |
| SS7215      |                         | 130 | 25 | 1.5   | 1        | 84                      | 121 | 1.5 | 0.165               |
| SS7916      | 80                      | 110 | 16 | 1     | 0.6      | 86                      | 104 | 1   | 0.054               |
| SS7016      |                         | 125 | 22 | 1.1   | 0.6      | 87                      | 118 | 1   | 0.12                |
| SS7216      |                         | 140 | 26 | 2     | 1        | 90                      | 130 | 2   | 0.196               |
| SS7017      | 85                      | 130 | 22 | 1.1   | 0.6      | 92                      | 123 | 1   | 0.127               |
| SS7217      |                         | 150 | 28 | 2     | 1        | 95                      | 140 | 2   | 0.242               |
| SS7918      | 90                      | 125 | 18 | 1.1   | 0.6      | 97                      | 118 | 1   | 0.081               |
| SS7018      |                         | 140 | 24 | 1.5   | 1        | 99                      | 131 | 1.5 | 0.165               |
| SS7919      | 95                      | 130 | 18 | 1.1   | 0.6      | 102                     | 123 | 1   | 0.083               |
| SS7019      |                         | 145 | 24 | 1.5   | 1        | 104                     | 136 | 1.5 | 0.171               |
| SS7920      | 100                     | 140 | 20 | 1.1   | 0.6      | 107                     | 133 | 1   | 0.115               |
| SS7020      |                         | 150 | 24 | 1.5   | 1        | 109                     | 141 | 1.5 | 0.178               |
| SS7921      | 105                     | 145 | 20 | 1.1   | 0.6      | 112                     | 138 | 1   | 0.118               |
| SS7922      | 110                     | 150 | 20 | 1.1   | 0.6      | 117                     | 143 | 1   | 0.124               |




Self-aligning stainless steel ball bearings



| Bearing No | Boundary dimensions (mm) |    |    |        | Mounting dimensions (mm) |      |     | Mass<br>(kg) (refer) |
|------------|--------------------------|----|----|--------|--------------------------|------|-----|----------------------|
|            |                          |    |    |        | da                       | Da   | ra  |                      |
|            | d                        | D  | B  | r min) | min                      | max  | max |                      |
| SS135      | 5                        | 19 | 6  | 0.3    | 7                        | 17   | 0.3 | 0.001633             |
| SS126      | 6                        | 19 | 6  | 0.3    | 8                        | 17   | 0.3 | 0.001633             |
| SS127      | 7                        | 22 | 7  | 0.3    | 9                        | 20   | 0.3 | 0.002567             |
| SS108      | 8                        | 22 | 7  | 0.3    | 10                       | 20   | 0.3 | 0.002567             |
| SS129      | 9                        | 26 | 8  | 0.6    | 13                       | 22   | 0.6 | 0.003967             |
| SS1200     | 10                       | 30 | 9  | 0.6    | 14                       | 26   | 0.6 | 0.006067             |
| SS2200     |                          | 30 | 14 | 0.6    | 14                       | 26   | 0.6 | 0.0084               |
| SS1300     |                          | 25 | 11 | 0.6    | 14                       | 31   | 0.6 | 0.0105               |
| SS2300     |                          | 25 | 17 | 0.6    | 14                       | 31   | 0.6 | 0.015167             |
| SS1201     | 12                       | 32 | 10 | 0.6    | 16                       | 28   | 0.6 | 0.007233             |
| SS2201     |                          | 32 | 14 | 0.6    | 16                       | 28   | 0.6 | 0.009567             |
| SS1301     |                          | 37 | 12 | 1      | 17                       | 32   | 1   | 0.012133             |
| SS2301     |                          | 37 | 17 | 1      | 17                       | 32   | 1   | 0.017033             |
| SS1202     | 15                       | 35 | 11 | 0.6    | 19                       | 31   | 0.6 | 0.008867             |
| SS2202     |                          | 35 | 14 | 0.6    | 19                       | 31   | 0.6 | 0.010733             |
| SS1302     |                          | 42 | 13 | 1      | 20                       | 37   | 1   | 0.0168               |
| SS2302     |                          | 42 | 17 | 1      | 20                       | 37   | 1   | 0.020533             |
| SS1203     | 17                       | 40 | 12 | 0.6    | 21                       | 36   | 0.6 | 0.013067             |
| SS2203     |                          | 40 | 16 | 0.6    | 21                       | 36   | 0.6 | 0.015867             |
| SS1303     |                          | 47 | 14 | 1      | 22                       | 42   | 1   | 0.023333             |
| SS2303     |                          | 47 | 19 | 1      | 22                       | 42   | 1   | 0.028                |
| SS1204     | 20                       | 47 | 14 | 1      | 25                       | 42   | 1   | 0.021                |
| SS2204     |                          | 47 | 18 | 1      | 25                       | 42   | 1   | 0.025667             |
| SS1304     |                          | 52 | 15 | 1.1    | 26.5                     | 45.5 | 1   | 0.030333             |
| SS1304     |                          | 52 | 21 | 1.1    | 26.5                     | 45.5 | 1   | 0.037333             |
| SS1205     | 25                       | 52 | 15 | 1      | 30                       | 47   | 1   | 0.025667             |
| SS2205     |                          | 52 | 18 | 1      | 30                       | 47   | 1   | 0.030333             |
| SS1305     |                          | 62 | 17 | 1.1    | 31.5                     | 55.5 | 1   | 0.046667             |
| SS2305     |                          | 62 | 24 | 1.1    | 31.5                     | 55.5 | 1   | 0.060667             |
| SS1206     | 30                       | 62 | 16 | 1      | 35                       | 57   | 1   | 0.039667             |
| SS2206     |                          | 62 | 20 | 1      | 35                       | 57   | 1   | 0.046667             |
| SS1306     |                          | 72 | 19 | 1.1    | 36.5                     | 65.5 | 1   | 0.07                 |
| SS2306     |                          | 72 | 27 | 1.1    | 36.5                     | 65.5 | 1   | 0.088667             |
| SS1207     | 35                       | 72 | 17 | 1.1    | 41.5                     | 65.5 | 1   | 0.058333             |
| SS2207     |                          | 72 | 23 | 1.1    | 41.5                     | 65.5 | 1   | 0.072333             |
| SS1307     |                          | 80 | 21 | 1.5    | 43                       | 72   | 1.5 | 0.091                |
| SS2307     |                          | 80 | 31 | 1.5    | 43                       | 72   | 1.5 | 0.121333             |


| Bearing No | Boundary dimensions (mm) |     |    |        | Mounting dimensions (mm) |      |     | Mass<br>(kg) (refer) |
|------------|--------------------------|-----|----|--------|--------------------------|------|-----|----------------------|
|            |                          |     |    |        | da                       | Da   | ra  |                      |
|            | d                        | D   | B  | r min) | min                      | max  | max |                      |
| SS1208     | 40                       | 80  | 18 | 1.1    | 46.5                     | 73.5 | 1   | 0.074667             |
| SS2208     |                          | 80  | 23 | 1.1    | 46.5                     | 73.5 | 1   | 0.091                |
| SS1308     |                          | 90  | 23 | 1.5    | 48                       | 82   | 1.5 | 0.128333             |
| SS2308     |                          | 90  | 33 | 1.5    | 48                       | 82   | 1.5 | 0.165667             |
| SS1209     | 45                       | 85  | 19 | 1.1    | 51.5                     | 78.5 | 1   | 0.084                |
| SS2209     |                          | 85  | 23 | 1.1    | 51.5                     | 78.5 | 1   | 0.098                |
| SS1309     |                          | 100 | 25 | 1.5    | 53                       | 92   | 1.5 | 0.172667             |
| SS2309     |                          | 100 | 36 | 1.5    | 53                       | 92   | 1.5 | 0.221667             |
| SS1210     | 50                       | 90  | 20 | 1.1    | 56.5                     | 83.5 | 1   | 0.093333             |
| SS2210     |                          | 90  | 23 | 1.1    | 56.5                     | 83.5 | 1   | 0.105                |
| SS1310     |                          | 110 | 27 | 2      | 59                       | 101  | 2   | 0.217                |
| SS2310     |                          | 110 | 40 | 2      | 59                       | 101  | 2   | 0.294                |
| SS1211     | 55                       | 100 | 21 | 1.5    | 63                       | 92   | 1.5 | 0.126                |
| SS2211     |                          | 100 | 25 | 1.5    | 63                       | 92   | 1.5 | 0.144667             |
| SS1311     |                          | 120 | 29 | 2      | 64                       | 111  | 2   | 0.284667             |
| SS2311     |                          | 120 | 43 | 2      | 64                       | 111  | 2   | 0.378                |
| SS1212     | 60                       | 110 | 22 | 1.5    | 68                       | 102  | 1.5 | 0.161                |
| SS2212     |                          | 110 | 28 | 1.5    | 68                       | 102  | 1.5 | 0.196                |
| SS1312     |                          | 130 | 31 | 2.1    | 71                       | 119  | 2   | 0.352333             |
| SS2312     |                          | 130 | 46 | 2.1    | 71                       | 119  | 2   | 0.466667             |
| SS1213     | 65                       | 120 | 23 | 1.5    | 73                       | 112  | 1.5 | 0.205333             |
| SS2213     |                          | 120 | 31 | 1.5    | 73                       | 112  | 1.5 | 0.261333             |
| SS1313     |                          | 140 | 33 | 2.1    | 76                       | 129  | 2   | 0.438667             |
| SS2313     |                          | 140 | 48 | 2.1    | 76                       | 129  | 2   | 0.578667             |
| SS1214     | 70                       | 125 | 24 | 1.5    | 78                       | 117  | 1.5 | 0.226333             |
| SS2214     |                          | 125 | 31 | 1.5    | 78                       | 117  | 1.5 | 0.273                |
| SS1314     |                          | 150 | 35 | 2.1    | 81                       | 139  | 2   | 0.536667             |
| SS2314     |                          | 150 | 51 | 2.1    | 81                       | 139  | 2   | 0.758333             |
| SS1215     | 75                       | 130 | 25 | 1.5    | 83                       | 122  | 1.5 | 0.245                |
| SS2215     |                          | 130 | 31 | 1.5    | 83                       | 122  | 1.5 | 0.291667             |
| SS1216     | 80                       | 140 | 26 | 2      | 89                       | 131  | 2   | 0.298667             |
| SS2216     |                          | 140 | 33 | 2      | 89                       | 131  | 2   | 0.361667             |
| SS1217     | 85                       | 150 | 28 | 2      | 94                       | 141  | 2   | 0.371                |
| SS2217     |                          | 150 | 36 | 2      | 94                       | 141  | 2   | 0.452667             |

Single direction thrust stainless steel ball bearings



| Bearing No | Boundary dimensions (mm) |     |    |         | Mounting dimensions (mm) |     | mass<br>(kg)<br>(refer) |
|------------|--------------------------|-----|----|---------|--------------------------|-----|-------------------------|
|            |                          |     |    |         | d1                       | D1  |                         |
|            | d                        | D   | T  | r (min) | max                      | min |                         |
| SS51100    | 10                       | 24  | 9  | 0.3     | 24                       | 11  | 0.004                   |
| SS51200    |                          | 26  | 11 | 0.6     | 26                       | 12  | 0.005                   |
| SS51101    | 12                       | 26  | 9  | 0.3     | 26                       | 13  | 0.004                   |
| SS51201    |                          | 28  | 11 | 0.6     | 28                       | 14  | 0.006                   |
| SS51102    | 15                       | 28  | 9  | 0.3     | 28                       | 16  | 0.004                   |
| SS51202    |                          | 32  | 12 | 0.6     | 32                       | 17  | 0.008                   |
| SS51103    | 17                       | 30  | 9  | 0.3     | 30                       | 18  | 0.004                   |
| SS51203    |                          | 35  | 12 | 0.6     | 35                       | 19  | 0.009                   |
| SS51104    | 20                       | 35  | 10 | 0.3     | 35                       | 21  | 0.007                   |
| SS51204    |                          | 40  | 14 | 0.6     | 40                       | 22  | 0.014                   |
| SS51105    | 25                       | 42  | 11 | 0.6     | 42                       | 26  | 0.01                    |
| SS51205    |                          | 47  | 15 | 0.6     | 47                       | 27  | 0.02                    |
| SS51106    | 30                       | 47  | 11 | 0.6     | 47                       | 32  | 0.011                   |
| SS51206    |                          | 52  | 16 | 0.6     | 52                       | 32  | 0.026                   |
| SS51107    | 35                       | 52  | 12 | 0.6     | 52                       | 37  | 0.014                   |
| SS51207    |                          | 62  | 18 | 1       | 62                       | 37  | 0.037                   |
| SS51108    | 40                       | 60  | 13 | 0.6     | 60                       | 42  | 0.021                   |
| SS51208    |                          | 68  | 19 | 1       | 68                       | 42  | 0.049                   |
| SS51109    | 45                       | 65  | 14 | 0.6     | 65                       | 47  | 0.026                   |
| SS51209    |                          | 73  | 20 | 1       | 73                       | 47  | 0.056                   |
| SS51110    | 50                       | 70  | 14 | 0.6     | 70                       | 52  | 0.028                   |
| SS51210    |                          | 78  | 22 | 1       | 78                       | 52  | 0.068                   |
| SS51111    | 55                       | 78  | 16 | 0.6     | 78                       | 57  | 0.04                    |
| SS51211    |                          | 90  | 25 | 1       | 90                       | 57  | 0.107                   |
| SS51112    | 60                       | 85  | 17 | 1       | 85                       | 62  | 0.051                   |
| SS51212    |                          | 95  | 26 | 1       | 95                       | 62  | 0.121                   |
| SS51113    | 65                       | 90  | 18 | 1       | 90                       | 67  | 0.058                   |
| SS51213    |                          | 100 | 27 | 1       | 100                      | 67  | 0.135                   |
| SS51114    | 70                       | 95  | 18 | 1       | 95                       | 72  | 0.063                   |
| SS51214    |                          | 105 | 27 | 1       | 105                      | 72  | 0.142                   |
| SS51115    | 75                       | 100 | 19 | 1       | 100                      | 77  | 0.07                    |
| SS51215    |                          | 110 | 27 | 1       | 110                      | 77  | 0.152                   |
| SS51116    | 80                       | 105 | 19 | 1       | 105                      | 82  | 0.075                   |
| SS51216    |                          | 115 | 28 | 1       | 115                      | 82  | 0.168                   |
| SS51117    | 85                       | 110 | 19 | 1       | 110                      | 87  | 0.079                   |
| SS51217    |                          | 125 | 31 | 1       | 125                      | 88  | 0.219                   |

Insert stainless steel bearing



| Bearing No | Boundary dimensions (mm) |     |      |      |     |       |     |            | Mass |         |
|------------|--------------------------|-----|------|------|-----|-------|-----|------------|------|---------|
|            | d                        | D   | B    | S    | C   | r/min | G   | ds         | (kg) | (refer) |
| SSUC201    | 12                       | 47  | 31   | 12.7 | 17  | 0.6   | 4.5 | M6 x 1     | 0.16 | 0.09    |
| SSUC202    | 15                       | 47  | 31   | 12.7 | 17  | 0.6   | 4.5 | M6 x 1     | 0.15 | 0.08    |
| SSUC203    | 17                       | 47  | 31   | 12.7 | 17  | 0.6   | 4.5 | M6 x 1     | 0.14 | 0.07    |
| SSUC204    | 20                       | 47  | 31   | 12.7 | 17  | 1     | 4.5 | M6 x 1     | 0.12 | 0.07    |
| SSUC205    | 25                       | 52  | 34.1 | 14.3 | 17V | 1     | 5   | M6 x 1     | 0.17 | 0.09    |
| SSUC206    | 30                       | 62  | 38.1 | 15.9 | 19  | 1     | 5   | M6 x 1     | 0.27 | 0.14    |
| SSUC207    | 35                       | 72  | 42.9 | 17.5 | 20  | 1.1   | 6   | M8 x 1     | 0.40 | 0.21    |
| SSUC208    | 40                       | 80  | 49.2 | 19   | 21  | 1.1   | 8   | M8 x 1     | 0.54 | 0.29    |
| SSUC209    | 45                       | 85  | 49.2 | 19   | 22  | 1.1   | 8   | M8 x 1     | 0.57 | 0.30    |
| SSUC210    | 50                       | 90  | 51.6 | 19   | 24  | 1.1   | 9   | M10 x 1    | 0.64 | 0.34    |
| SSUC211    | 55                       | 100 | 55.6 | 22.2 | 25  | 1.5   | 9   | M10 x 1    | 0.89 | 0.48    |
| SSUC212    | 60                       | 110 | 65.1 | 25.4 | 27  | 1.5   | 10  | M10 x 1    | 1.20 | 0.64    |
| SSUC213    | 65                       | 120 | 65.1 | 25.4 | 27  | 1.5   | 10  | M10 x 1    | 1.51 | 0.80    |
| SSUC214    | 70                       | 125 | 74.6 | 30.2 | 29  | 1.5   | 12  | M12 x 1.25 | 1.68 | 0.89    |
| SSUC215    | 75                       | 130 | 77.8 | 33.3 | 30  | 1.5   | 12  | M12 x 1.25 | 1.86 | 0.99    |
| SSUC216    | 80                       | 140 | 82.6 | 33.3 | 33  | 2     | 14  | M12 x 1.25 | 2.17 | 1.16    |
| SSUC217    | 85                       | 150 | 85.7 | 34.1 | 36  | 2     | 14  | M12 x 1.25 | 2.62 | 1.39    |
| SSUC218    | 90                       | 160 | 96   | 39.7 | 37  | 2     | 14  | M12 x 1.25 | 3.31 | 1.76    |
| SSUC220    | 100                      | 180 | 108  | 42   | 41  | 2     | 14  | M12 x 1.25 | 3.46 | 1.85    |



Ningbo Accor Machinery (Bearings) Co Ltd

Add: 4F, 675 Shiji Avenue, Jiangdong, Ningbo 315040, China

Ph: +86 574 87939850, 87939855

Fax: +86 574 87939860

E-mail: [accor@accomachinery.com.cn](mailto:accor@accomachinery.com.cn)

[http:// www.accorbearings.com](http://www.accorbearings.com) , [www.accomachinery.com](http://www.accomachinery.com)